



Caution:

- ◆ **Warning: This manual should be fully read and understood before starting installation!**
- ◆ **Power supply 230 V 50/60 Hz!**
- ◆ **Run cooling unit always with correct oil level otherwise damage of pump may occur!**
- ◆ **Never operate damaged or leaking equipment!**
- ◆ **Before starting any service work disconnect the cooling unit from the power source!**

Laird Technologies GmbH
Borsigstraße 1
D-24568 Kaltenkirchen
Phone: +49(0)4191-999 30
Fax: +49(0)4191-999 333
Email: info-lcs@Lairdtech.com
Homepage: www.Lairdtech.com

Table of contents	Page
1. Description	2
2. Technical data	3
2.1 Physical dimensions	3
2.2 Performance data	3
2.3 Environment specifications	3
2.4 Settings	3
3. Setting to work	4
4. Maintenance	4
5. Putting out of operation.	4
6. Spare part list and illustrations	5
7. Cooling performance	7
8. Flow Chart and Circuite Diagram.....	8
9. Declaration of Conformity	10

1. Description

The cooling unit OW 4002 is intended for the cooling of an oil circuit. Oil circulates between the cooling unit and the heat source. The oil is re-cooled by a water-cooled heat exchanger. Cooling hoses are connected to the cooling unit via screw and via hose nipples.

Coolant inlet and outlet are marked with symbols: Inlet: $\downarrow \bigcirc$, outlet $\uparrow \bigcirc$

The oil flow is monitored by an adjustable flow switch, the oil temperature by an adjustable thermal switch. The signals of the flow switch and the thermal switch are available at a potential free safety circuit. The oil pressure is limited by an adjustable bypass valve. The capacity of the cooling unit depends on the temperature difference between the cooling water temperature and the oil outlet temperature.

You can take it from diagram on page 7

Inlet: $\downarrow \bigcirc$ outlet: $\uparrow \bigcirc$

2. Technical data

2.1 Physical dimensions

Length:	621 mm
Width:	350 mm
Height:	551 mm
Weight:	ca. 45 kg without oil
Fuel capacity oil:	app. 23 l

2.2 Performance data

Cooling capacity:	4000 W,
Oil flow:	> 17 l/min at 3,5 bar related to oil temperature $22^{\circ}\text{C} \pm 3^{\circ}\text{C}$
Voltage rating:	$230\text{V} \pm 10\%$ / 50/60 Hz
Current consumption :	3,6 A by 6 bar
Noise level:	60 dB (A) (50 Hz) distance 1 m in any direction

2.3 Environment specifications

Ambient temperature:	$+5^{\circ}\text{C} \dots +40^{\circ}\text{C}$
Storage temperature:	$-40^{\circ}\text{C} \dots +70^{\circ}\text{C}$ without coolant
Air humidity:	20%...80%

2.4 Settings

System pressure:	9,0 bar
Flow switch:	17,0 l/min
Temp. controller (on)	55°C

3. Setting to work

Remove cover

Remove cap of oil reservoir and fill with oil up to the visible mark

Connect oil hoses to cooler.

Connect water supply to cooler.

Establish electrical connections according wiring diagram, use suitable leads.

Start water supply to cooler.

Start power supply for cooler

Exhaust valve open

Run oil cooler for approximately 10 minutes to
remove air from the oil circuit.

Exhaust valve close


Check oil level and refill if necessary

Stop cooling unit

Close cap of oil reservoir.

Mount cover.

Cooling unit is ready for use.



Inspection glass

4. Maintenance

Check oil level at inspection glass monthly or more often, if necessary and refill oil.




5. Putting out of operation.

- Stop oil circulation by switching off pump.
- Disconnect equipment from mains.
- Lock oil supply and return pipes.
- Lock cooling water supply and return pipes.
- Drain water off the cooling system for frost.

6. Spare part list and illustrations


No.	Description	Code number
1	engine pump unit KA-1-26-230-2	95205237.00
2	motor capacitor	95290735.00
3	safety valve Type 618 T	96121014.00
4	flow controller FW1	95140572.00
5	switch head	95140567.00
6	temperature controller water 25-65°C	95100101.00
7	thermostat AMFS-13	95160001.00
8	strainer 125 µm	93314901.00
9	filler neck	95169901.00
10	inspection glass	93300201.00

Manual OW 4002



7. Cooling performance

Cooling performance 4,0 kW, oil temperature vs. water temperature and flow rate




T_w = Temperature Water inlet


$P1$ = Pressure Water inlet


$P2$ = Pressure Water outlet


Pressure drop = $P1 - P2$



Connector distances







Konformitätserklärung *Declaration of Conformity*

Wir: Laird Technologies GmbH
We: (Name des Hersteller / *supplier's name*)

Borsigstrasse 1
24568 Kaltenkirchen
Deutschland / Germany

Erklären in alleiniger Verantwortung, dass das Produkt
Declare under our sole responsibility that the product

Kühlaggregate
Cooling aggregate

Modelle / *types* **WL, WLK, OL, OLK, OW, WW**

auf das sich die Erklärung bezieht / *to which this declaration relates,*
mit den folgenden Normen oder normativen Dokumenten übereinstimmt,
is in conformity with the following standards or normative documents

DIN EN ISO 12100-1 (2004-04)
DIN EN ISO 12100-2 (2004-04)
DIN EN 60204-1 (2009-10)
DIN EN 349 (2009-09)

Gemäß den Bestimmungen der Richtlinie 2006/42/EG
Following the provisions of directive 2006/42/EEC

Kaltenkirchen
2010-12-23

Ort / Datum / der Ausstellung
Place / date of issue

Leiter Qualitätsmanagement
Leader Qualitymanagement

Funktion
Responsibility

Lothar Lühr



Name / Unterschrift
Name/ signature